


## ANSI B92.1



Profil	Abmessung [P/Ps Teeth]	$\alpha$	Räumkapazität	Vorbohrung [mm]
ANSI B92.1	12/24 Z=17	30°	32-80 mm	33.70 G9
ANSI B92.1	12/24 Z=14	30°	85 mm	27.6 H7
ANSI B92.1	16/32 Z=9	30°	20-50 mm	12.85 H9
ANSI B92.1	16/32 Z=11	30°	50 mm	16.15 H9
ANSI B92.1	16/32 Z=12	30°	26 mm	17.5 H9
ANSI B92.1	16/32 Z=13	30°	16-50 mm	18.90 G9
ANSI B92.1	16/32 Z=14	30°	16-32 mm	20.50 G9
ANSI B92.1	16/32 Z=17	30°	16-50 mm	25.4 H9
ANSI B92.1	16/32 Z=20	30°	25-62 mm	30 G9
ANSI B92.1	16/32 Z=21	30°	25-62 mm	31.6 G9
ANSI B92.1	16/32 Z=23	30°	160 mm	35 H9
ANSI B92.1	48/96 Z=8	30°	21 mm	3.95 H9
ANSI B92.1	16/32 Z=15	30°	16-32 mm	22.10 H9